



### **Product description**

Order number	60.9921.808
Product description	Screw cap tube, working volume: 10 ml, (LxØ): 97 x 16 mm, material: PP, flat base, translucent, HD-PE, cap: natural, cap enclosed, 100 piece(s)/bag

### **Product characteristics**

Graduation	no
Cap	standard screw cap
Closure type	screw cap
Base shape	flat base
Volume of work	10 ml
Centrifugation max (RCF)	5000 x g
Centrifugation temperature	21
Centrifugation time	15 Min

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.





### **Size**

Diameter	16 mm
Length of product	97 mm

### **Material & colours**

Product material	Polypropylene (PP)
Colour of product	translucent
Closure material	High Density Polyethylene (HD-PE)
Colour of cap	natural
Tube material	Polypropylene (PP)

### **Purity & certification**

Satisfies the requirement	sealed at 18"hg/10min
Latex-free	yes
Safety data sheet	no

### **Packaging**

Minimum order qty.	1000
Type of smallest subpackaging	bag
Piece(s) / inner box	100
Piece (s) / outer case	1000
Piece(s) / pallet	40000
Depth of case	604 mm
Width of case	264 mm
Height of case	373 mm
Weight of product	0 g
Weight of case	7.2 kg
EAN of inner box	4038917151016
EAN case	4038917037211

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

